



Abrasive papers SiC EXCELLENCE

Available from P80 to P1200 from Ø 200 to 300 mm

The standard checks of abrasive papers generally manufactured in large quantities are sometimes insufficient to avoid that complete series of discs are outside the standard required by our Metallography laboratory.

LAM PLAN creates the Excellence Range and its double guarantee, every single paper is individually checked before packing.

Ø 200 mm

Self-adhesive			Non-adhesive	
Grains FEPA	Ref.	Ref.	Ref.	Ref.
P80	05 10080 20	05 00080 20	05 10080 30	05 00080 30
P120	05 10120 20	05 00120 20	05 10120 30	05 00120 30
P180	05 10180 20	05 00180 20	05 10180 30	05 00180 30
P240	05 10240 20	05 00240 20	05 10240 30	05 00240 30
P320	05 10320 20	05 00320 20	05 10320 30	05 00320 30
P400	05 10400 20	05 00400 20	05 10400 30	05 00400 30
P600	05 10600 20	05 00600 20	05 10600 30	05 00600 30
P1200	05 11200 20	05 01200 20	05 11200 30	05 01200 30

Ø 230 mm

50 pieces box

Ø 250 mm

Self-adhesive			Non-adhesive	
Grains FEPA	Ref.	Ref.	Ref.	Ref.
P80	05 10080 40	05 00080 40	05 10080 50	05 00080 50
P120	05 10120 40	05 00120 40	05 10120 50	05 00120 50
P180	05 10180 40	05 00180 40	05 10180 50	05 00180 50
P240	05 10240 40	05 00240 40	05 10240 50	05 00240 50
P320	05 10320 40	05 00320 40	05 10320 50	05 00320 50
P400	05 10400 40	05 00400 40	05 10400 50	05 00400 50
P600	05 10600 40	05 00600 40	05 10600 50	05 00600 50
P1200	05 11200 40	05 01200 40	05 11200 50	05 01200 50

Ø 300 mm

50 pieces box

Grinding wheels

LAM PLAN grinding wheels are used to dress samples in high speed automatic prepolishing machines. Two types available: Al_2O_3 grain 60 and SiC grain 150.



Al_2O_3 - GRAIN 60

Application	Lubricant	Ø in mm	Ref.
For grinding of soft, ductile materials <HV200	Water	355	05 M0060 80

SIC - GRAIN 150

Application	Lubricant	Ø in mm	Ref.
For grinding of all materials >HV200	Water	355	05 M0150 80